

STARPOINT VRS-20t-M64

Artikel-Nr: 7907509



- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Available as: - Standard Metric Thread (DIN EN 13)
- Significant product characteristics of the VRS are subject to property right claims.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- For permanent installation and recurrend lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-20t-M64

Artikel-Nr: 7907509



| | | |
|--------------------|----------|-----------|
| weight | 16.41 kg | 36.18 lbs |
| Nominal WLL | 20000 kg | 44090 lbs |
| T | 177 mm | 6-31/32" |
| B | 55 mm | 2-5/32" |
| C | 49 mm | 1-15/16" |
| D | 120 mm | 4-3/4" |
| E | 121 mm | 4-3/4" |
| G | 158 mm | 6-1/4" |
| I | 90 mm | 3-17/32" |
| K | 229 mm | 9" |
| L | 96 mm | 3-25/32" |
| M | M64 mm | M64 |
| N | 36 mm | 1-27/64" |