

PowerPoint PP-VIP8-2,5t-M20

Artikel-Nr: 7989527



- **Universal and non-mix-up clevis connection for chains, hooks and eye.**
- **Double ball bearing** is the optimal solution for turning and flipping operations under full load (not suitable for permanent turning under load).
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction** Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Marking with requested torque moment and nominal WLL with a safety factor of 4:1 (MRL 2006/42/EG) and 5:1 (ASME B 30.26).
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2023-06, Certificate-No.: HM 240065
- Significant product characteristics of the PP-S, PP-B and PP-VIP are subject to property right claims.
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint PP-VIP8-2,5t-M20

Artikel-Nr: 7989527



weight	0.94 kg	2.09 lbs
Nominal WLL	2500 kg	5500 lbs
T	61 mm	2-13/32"
A	8 mm	5/16"
D	61 mm	2-13/32"
E	55 mm	2-5/32"
F	30 mm	1-3/16"
M	M20 mm	M20