

STARPOINT VRS-7t-1 1/2"-8UN

Artikel-Nr: 7991917



- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Variable bolt lengths available for tapped or through holes.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread 8UN (ANSI B1.1) - Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts Version VRS-F).
- For permanent installation and recurrent lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-7t-1 1/2"-8UN

Artikel-Nr: 7991917



| | | |
|--------------------|---------------|------------|
| weight | 3.35 kg | 7.39 lbs |
| Nominal WLL | 7000 kg | 15430 lbs |
| T | 104 mm | 4-3/32" |
| B | 32 mm | 1-1/4" |
| C | 29 mm | 1-5/32" |
| D | 73 mm | 2-7/8" |
| E | 76 mm | 3" |
| G | 98 mm | 3-27/32" |
| I | 53 mm | 2-3/32" |
| K | 135 mm | 5-5/16" |
| L | 54 mm | 2-1/8" |
| M | 1 1/2"-8UN mm | 1 1/2"-8UN |
| N | 7/8" mm | 7/8" |