

STARPOINT VRS-7t-M36X3

Artikel-Nr: 7992728



- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Available as: - Standard Metric Thread (DIN EN 13)
- Significant product characteristics of the VRS are subject to property right claims.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- For permanent installation and recurrend lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-7t-M36X3

Artikel-Nr: 7992728



weight	3.50 kg	7.72 lbs
Nominal WLL	7000 kg	15430 lbs
T	104 mm	4-1/16"
B	32 mm	1-1/4"
C	29 mm	1-5/32"
D	73 mm	2-27/32"
E	76 mm	3"
G	98 mm	3-13/16"
I	53 mm	2-3/32"
K	135 mm	5-5/16"
L	54 mm	2-1/8"
M	M36X3 mm	M36X3
N	22 mm	7/8"