

INOX-STAR[®]-Eyebolt M20 - L=60

Artikel-Nr: 7998714






- Body and bolt made out of Duplex Steel 1.4462 (high resistancy in sea water and in environment with a high concentration of chlorine ions).
- Pentagonal shape for a clear determination to common lifting points (i.e. eye bolts).
- Lifting points pivots 360° for an easy adjustment in load direction.
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Non removable special bolt (this reduces the risk of non standard bolts).
- Clear marking at the bolt head: RUD, thread size, batch-no., class of strength.
- Available as: Standard Metric Thread (DIN EN 13)
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- For permanent installation and recurrend lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

INOX-STAR[®]-Eyebolt M20 - L=60

Artikel-Nr: 7998714



weight	0.60 kg	1.32 lbs
Nominal WLL	2000 kg	4400 lbs
T	58 mm	2-1/4"
B	19 mm	3/4"
C	16 mm	5/8"
D	40 mm	1-9/16"
E	43 mm	1-21/32"
G	47 mm	1-7/8"
I	27,5 mm	1-5/32"
K	74 mm	2-29/32"
L	60 mm	2-3/8"
M	M20 mm	M20
N	12 mm	15/32"