

PowerPoint PP-VIP16-8t-1 1/2"-6BSW

Artikel-Nr: 8600305



Connection only with RUD approved components e.g; VCÖH-16, oval link, PP 8t or the 16 mm VIP chain.

Hint : The VIP chain connection is fool proof. When assembling the components, pay attention to the correct WLL allocation.

- **Can be combined with most commercial lifting means without additional connecting element.**
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction**Lowest kinking possibility due to cardan joint.
- **Suspension ring with enlarged pivoting area.**
- Clear marking of the minimum WLL for all loading directions.
- Variable thread lengths are available for use of threaded holes and through hole fixtures.
- Non removable special bolt (this reduces the risk of non standard bolts).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint PP-VIP16-8t-1 1/2"-6BSW

Artikel-Nr: 8600305



weight	4.74 kg	10.45 lbs
Nominal WLL	8000 kg	17630 lbs
T	102 mm	4"
A	16 mm	5/8"
D	100 mm	3-15/16"
E	90 mm	3-17/32"
F	54 mm	2-1/8"
M	1 1/2"-6BSW mm	1 1/2"-6BSW