

PowerPoint PP-VIP8-2,5t-G1/2"

Artikel-Nr: 8600573



Connection only with RUD approved components e.g; VCÖH-8, oval link, PP 2,5t or the 8 mm VIP chain.

Hint : The VIP chain connection is fool proof. When assembling the components, pay attention to the correct WLL allocation.

- **Can be combined with most commercial lifting means without additional connecting element.**
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction**Lowest kinking possibility due to cardan joint.
- **Suspension ring with enlarged pivoting area.**
- Clear marking of the minimum WLL for all loading directions.
- Variable thread lengths are available for use of threaded holes and through hole fixtures.
- Non removable special bolt (this reduces the risk of non standard bolts).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint PP-VIP8-2,5t-G1/2"

Artikel-Nr: 8600573



weight	0.93 kg	2.05 lbs
Nominal WLL	2500 kg	5500 lbs
T	61 mm	2-13/32"
A	8 mm	5/16"
D	61 mm	2-13/32"
E	55 mm	2-5/32"
F	22-30 mm	22-30
M	G 1/2" mm	G 1/2"