

## PowerPoint PP-VIP10-4t-G3/4"

Artikel-Nr: 8600574



Connection only with RUD approved components e.g; VCÖH-10, oval link, PP 4t or the 10 mm VIP chain.

Hint : The VIP chain connection is fool proof. When assembling the components, pay attention to the correct WLL allocation.

- **Can be combined with most commercial lifting means without additional connecting element.**
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction**Lowest kinking possibility due to cardan joint.
- **Suspension ring with enlarged pivoting area.**
- Clear marking of the minimum WLL for all loading directions.
- Variable thread lengths are available for use of threaded holes and through hole fixtures.
- Non removable special bolt (this reduces the risk of non standard bolts).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## PowerPoint PP-VIP10-4t-G3/4"

Artikel-Nr: 8600574



<b>weight</b>	1.83 kg	4.03 lbs
<b>Nominal WLL</b>	4000 kg	8820 lbs
<b>T</b>	77 mm	3"-1/32"
<b>A</b>	10 mm	3/8"
<b>D</b>	78 mm	3-1/16"
<b>E</b>	70 mm	2-3/4"
<b>F</b>	27-36 mm	27-36
<b>M</b>	G 3/4" mm	G 3/4"