

# NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount



## Applications

Designed for use as electrical junction boxes, terminal wiring boxes, instrument housings, and electrical control enclosures. Provides protection from dust, dirt, oil and water.

## Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth— no holes or knockouts
- Captivated cover screws thread into sealed wells.
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.

## Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

|          |             |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

### NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount

| Part Number                  | Price    | Size<br>HxWxD                           | Drawing<br>Link     | Optional<br>Subpanel      | Price   |
|------------------------------|----------|---|---------------------|---------------------------|---------|
| <a href="#">SCE-404SC</a>    | \$48.50  | 4.44 x 4.31 x 3.15 [113 x 109 x 80]     | <a href="#">PDF</a> | —                         | —       |
| <a href="#">SCE-4044SC</a>   | \$48.50  | 4.44 x 4.31 x 4.15 [113 x 109 x 105]    | <a href="#">PDF</a> | —                         | —       |
| <a href="#">SCE-604SC</a>    | \$55.00  | 6.44 x 4.31 x 3.15 [164 x 109 x 80]     | <a href="#">PDF</a> | <a href="#">SCE-6P4</a>   | \$4.25  |
| <a href="#">SCE-6044SC</a>   | \$61.00  | 6.44 x 4.31 x 4.15 [164 x 109 x 105]    | <a href="#">PDF</a> | <a href="#">SCE-6P4</a>   | \$4.25  |
| <a href="#">SCE-606SC</a>    | \$65.00  | 6.44 x 6.31 x 4.15 [164 x 160 x 105]    | <a href="#">PDF</a> | <a href="#">SCE-6P6</a>   | \$5.00  |
| <a href="#">SCE-806SC</a>    | \$68.00  | 8.44 x 6.31 x 3.65 [214 x 160 x 93]     | <a href="#">PDF</a> | <a href="#">SCE-8P6</a>   | \$5.75  |
| <a href="#">SCE-8066SC</a>   | \$77.00  | 8.44 x 6.31 x 6.15 [214 x 160 x 156]    | <a href="#">PDF</a> | <a href="#">SCE-8P6</a>   | \$5.75  |
| <a href="#">SCE-808SC</a>    | \$77.00  | 8.44 x 8.31 x 4.15 [214 x 211 x 105]    | <a href="#">PDF</a> | <a href="#">SCE-8P8</a>   | \$6.75  |
| <a href="#">SCE-1008SC</a>   | \$84.00  | 10.44 x 8.31 x 4.15 [265 x 211 x 105]   | <a href="#">PDF</a> | <a href="#">SCE-10P8</a>  | \$8.00  |
| <a href="#">SCE-10086SC</a>  | \$95.00  | 10.44 x 8.31 x 6.15 [265 x 211 x 156]   | <a href="#">PDF</a> | <a href="#">SCE-10P8</a>  | \$8.00  |
| <a href="#">SCE-1010SC</a>   | \$94.00  | 10.44 x 10.31 x 4.15 [265 x 262 x 105]  | <a href="#">PDF</a> | <a href="#">SCE-10P10</a> | \$9.25  |
| <a href="#">SCE-10106SC</a>  | \$105.00 | 10.44 x 10.31 x 6.15 [265 x 262 x 156]  | <a href="#">PDF</a> | <a href="#">SCE-10P10</a> | \$9.25  |
| <a href="#">SCE-1210SC</a>   | \$106.00 | 12.44 x 10.31 x 5.15 [316 x 262 x 131]  | <a href="#">PDF</a> | <a href="#">SCE-12P10</a> | \$10.75 |
| <a href="#">SCE-1212SC</a>   | \$124.00 | 12.44 x 12.31 x 6.15 [316 x 313 x 156]  | <a href="#">PDF</a> | <a href="#">SCE-12P12</a> | \$12.50 |
| <a href="#">SCE-121010SC</a> | \$161.00 | 12.44 x 10.31 x 10.15 [316 x 262 x 258] | <a href="#">PDF</a> | <a href="#">SCE-12P10</a> | \$10.75 |
| <a href="#">SCE-1412SC</a>   | \$136.00 | 14.44 x 12.31 x 6.15 [367 x 313 x 156]  | <a href="#">PDF</a> | <a href="#">SCE-14P12</a> | \$14.00 |
| <a href="#">SCE-1614SC</a>   | \$158.00 | 16.44 x 14.31 x 6.15 [418 x 363 x 156]  | <a href="#">PDF</a> | <a href="#">SCE-16P14</a> | \$27.50 |

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount



## Dimensions

