

NEMA 1 Single-Door Wall-Mount



Applications

Designed to house electrical controls, instruments, and components in areas that do not require oil, water and dust tight protection.

Construction

- 14-gauge, 16-gauge, or 18-gauge carbon steel depending on size
 - See drawings for details
- Spot weld construction
- Standoffs are provided for mounting optional subpanels.
- Butt hinge
- Doors open 180°
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Ground stud on door and body
- Mounting holes in back of enclosure
- Subpanel mounting hardware included
- Optional mounting straps are available.

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 1
- cULus Listed Type 1
- IEC 60529 IP30



NEMA 1 Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 1 Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-6N604LP	\$45.50	6.38 x 6.38 x 4.12 [162 x 162 x 105]	PDF	SCE-6N6MP	\$4.25
SCE-8N604LP	\$50.00	8.38 x 6.38 x 4.12 [213 x 162 x 105]	PDF	SCE-8N6MP	\$5.00
SCE-8N804LP	\$55.00	8.38 x 8.38 x 4.12 [213 x 213 x 105]	PDF	SCE-8N8MP	\$5.75
SCE-8N806LP	\$62.00	8.38 x 8.38 x 6.12 [213 x 213 x 155]	PDF	SCE-8N8MP	\$5.75
SCE-10N804LP	\$61.00	10.38 x 8.38 x 4.12 [264 x 213 x 105]	PDF	SCE-10N8MP	\$6.75
SCE-10N806LP	\$69.00	10.38 x 8.38 x 6.12 [264 x 213 x 155]	PDF	SCE-10N8MP	\$6.75
SCE-10N1004LP	\$62.00	10.38 x 10.38 x 4.12 [264 x 264 x 105]	PDF	SCE-10N10MP	\$8.00
SCE-10N1006LP	\$76.00	10.38 x 10.38 x 6.12 [264 x 264 x 155]	PDF	SCE-10N10MP	\$8.00
SCE-12N1004LP	\$73.00	12.38 x 10.38 x 4.12 [314 x 264 x 105]	PDF	SCE-12N10MP	\$9.00
SCE-12N1006LP	\$83.00	12.38 x 10.38 x 6.12 [314 x 264 x 155]	PDF	SCE-12N10MP	\$9.00
SCE-12N1204LP	\$80.00	12.38 x 12.38 x 4.12 [314 x 314 x 105]	PDF	SCE-12N12MP	\$10.75
SCE-12N1206LP	\$91.00	12.38 x 12.38 x 6.12 [314 x 314 x 155]	PDF	SCE-12N12MP	\$10.75
SCE-12N1208LP	\$101.00	12.38 x 12.38 x 8.12 [314 x 314 x 206]	PDF	SCE-12N12MP	\$10.75
SCE-14N1204LP	\$87.00	14.38 x 12.38 x 4.12 [365 x 314 x 105]	PDF	SCE-14N12MP	\$12.00
SCE-14N1206LP	\$99.00	14.38 x 12.38 x 6.12 [365 x 314 x 155]	PDF	SCE-14N12MP	\$12.00
SCE-14N1208LP	\$110.00	14.38 x 12.38 x 8.12 [365 x 314 x 206]	PDF	SCE-14N12MP	\$12.00
SCE-16N1206LP	\$148.00	16.38 x 12.38 x 6.12 [416 x 314 x 155]	PDF	SCE-16N12MP	\$17.50
SCE-16N1208LP	\$161.00	16.38 x 12.38 x 8.12 [416 x 314 x 206]	PDF	SCE-16N12MP	\$17.50
SCE-16N1606LP	\$165.00	16.38 x 16.38 x 6.12 [416 x 416 x 155]	PDF	SCE-16N16MP	\$29.00
SCE-16N1608LP	\$180.00	16.38 x 16.38 x 8.12 [416 x 416 x 206]	PDF	SCE-16N16MP	\$29.00
SCE-16N2006LP	\$183.00	16.38 x 20.38 x 6.12 [416 x 518 x 155]	PDF	SCE-20N16MP	\$32.50
SCE-20N1606LP	\$183.00	20.38 x 16.38 x 6.12 [518 x 416 x 155]	PDF	SCE-20N16MP	\$32.50
SCE-20N1608LP	\$200.00	20.38 x 16.38 x 8.12 [518 x 416 x 206]	PDF	SCE-20N16MP	\$32.50
SCE-20N2006LP	\$201.00	20.38 x 20.38 x 6.12 [518 x 518 x 155]	PDF	SCE-20N20MP	\$42.00
SCE-20N2008LP	\$220.00	20.38 x 20.38 x 8.12 [518 x 518 x 206]	PDF	SCE-20N20MP	\$42.00
SCE-20N2010LP	\$239.00	20.38 x 20.38 x 10.12 [518 x 518 x 257]	PDF	SCE-20N20MP	\$42.00
SCE-24N1606LP	\$199.00	24.38 x 16.38 x 6.12 [619 x 416 x 155]	PDF	SCE-24N16MP	\$34.50
SCE-24N2006LP	\$222.00	24.38 x 20.38 x 6.12 [619 x 518 x 155]	PDF	SCE-24N20MP	\$48.00
SCE-24N2008LP	\$243.00	24.38 x 20.38 x 8.12 [619 x 518 x 206]	PDF	SCE-24N20MP	\$48.00
SCE-24N2406LP	\$225.00	24.38 x 24.38 x 6.12 [619 x 619 x 155]	PDF	SCE-24N24MP	\$56.00
SCE-24N2408LP	\$248.00	24.38 x 24.38 x 8.12 [619 x 619 x 206]	PDF	SCE-24N24MP	\$56.00
SCE-24N2010LP	\$264.00	24.38 x 20.38 x 10.12 [619 x 518 x 257]	PDF	SCE-24N20MP	\$48.00
SCE-24N2412LP	\$293.00	24.38 x 24.38 x 12.12 [619 x 619 x 308]	PDF	SCE-24N24MP	\$56.00
SCE-30N2406LP	\$250.00	30.38 x 24.38 x 6.12 [772 x 619 x 155]	PDF	SCE-30N24MP	\$66.00
SCE-30N2408LP	\$278.00	30.38 x 24.38 x 8.12 [772 x 619 x 206]	PDF	SCE-30N24MP	\$66.00
SCE-30N2412LP	\$327.00	30.38 x 24.38 x 12.12 [772 x 619 x 308]	PDF	SCE-30N24MP	\$66.00
SCE-30N3008LP	\$314.00	30.38 x 30.38 x 8.12 [772 x 772 x 206]	PDF	SCE-30N30MP	\$88.00
SCE-36N2406LP	\$291.00	36.38 x 24.38 x 6.12 [924 x 619 x 155]	PDF	SCE-36N24MP	\$80.00
SCE-36N2408LP	\$320.00	36.38 x 24.38 x 8.12 [924 x 619 x 206]	PDF	SCE-36N24MP	\$80.00
SCE-36N2412LP	\$370.00	36.38 x 24.38 x 12.12 [924 x 619 x 308]	PDF	SCE-36N24MP	\$80.00
SCE-36N3006LP	\$319.00	36.38 x 30.38 x 6.12 [924 x 772 x 155]	PDF	SCE-36N30MP	\$106.00
SCE-36N3008LP	\$350.00	36.38 x 30.38 x 8.12 [924 x 772 x 206]	PDF	SCE-36N30MP	\$106.00
SCE-36N3012LP	\$413.00	36.38 x 30.38 x 12.12 [924 x 772 x 308]	PDF	SCE-36N30MP	\$106.00

Note: Dimensions in inches [millimeters].