

NEMA 4, 12, and 13 Wall-Mount Pushbutton



Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

Construction

- 16-gauge carbon steel
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm]
- Fully-removable cover
- Poured-in-place oil- and water-resistant gasket
- Welded mounting provision top and bottom of back

Finish

- ANSI 61 gray or RAL 1018 yellow powder coated inside and out

Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Wall-Mount Pushbutton

ANSI 61 Gray			RAL 1018 Yellow		Size HxWxD	Holes	Drawing Link
22mm	30mm	Price	30mm	Price			
SCE-1PBI	SCE-1PB	\$56.00	SCE-1PB-RAL1018	\$69.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	1	PDF
SCE-2PBI	SCE-2PB	\$65.00	SCE-2PB-RAL1018	\$79.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	2	PDF
SCE-3PBI	SCE-3PB	\$73.00	SCE-3PB-RAL1018	\$89.00	8.31 x 3.56 x 2.91 [211 x 90 x 74]	3	PDF
SCE-4PBI	SCE-4PB	\$81.00	SCE-4PB-RAL1018	\$98.00	10.56 x 3.56 x 2.91 [268 x 90 x 74]	4	PDF
SCE-4SPBI	SCE-4SPB	\$90.00	—	—	7.56 x 6.56 x 3.16 [192 x 167 x 80]	4	PDF
SCE-5PBI	SCE-5PB	\$89.00	SCE-5PB-RAL1018	\$108.00	12.81 x 3.56 x 2.91 [325 x 90 x 74]	5	PDF
SCE-6PBI	SCE-6PB	\$103.00	—	—	9.81 x 6.56 x 3.16 [249 x 167 x 80]	6	PDF
SCE-6PBVLI	SCE-6PBVL	\$97.00	—	—	15.06 x 3.56 x 2.91 [383 x 90 x 74]	6	PDF
SCE-8PBI	SCE-8PB	\$116.00	—	—	20.56 x 3.56 x 2.91 [522 x 90 x 74]	8	PDF
SCE-9PBI	SCE-9PB	\$119.00	—	—	9.81 x 8.81 x 3.16 [249 x 224 x 80]	9	PDF
SCE-12PBI	SCE-12PB	\$134.00	—	—	12.06 x 8.81 x 3.16 [306 x 224 x 80]	12	PDF

Note: Dimensions in inches [millimeters].

NEMA 4, 12, and 13 Wall-Mount Pushbutton



Dimensions

