

NEMA 4, 12, and 13 22mm Wall-Mount Pushbutton



Applications

Designed to offer protection for miniature oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

Construction

- 16-gauge carbon steel
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way miniature pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
 - Hole diameter is 0.87in [22.5 mm]
- Fully-removable cover
- Poured-in-place oil- and water-resistant gasket
- Welded mounting provision top and bottom of back

Finish

- ANSI 61 gray powder coated inside and out

Listings

- NEMA Type 4, 12 and 13
- cuULlisted Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 22mm Wall-Mount Pushbutton

Part Number	Price	Size HxWxD	Holes	Drawing Link
SCE-1PBGX	\$65.00	3.56 x 3.56 x 3.66 [90 x 90 x 93]	1	PDF
SCE-2PBGX	\$71.00	5.44 x 3.56 x 3.66 [138 x 90 x 93]	2	PDF
SCE-3PBGX	\$79.00	7.31 x 3.56 x 3.66 [186 x 90 x 93]	3	PDF
SCE-4PBGX	\$87.00	9.19 x 3.56 x 3.66 [233 x 90 x 93]	4	PDF
SCE-6PBGX	\$111.00	8.81 x 6.31 x 4.56 [224 x 160 x 116]	6	PDF
SCE-9PBGX	\$123.00	8.81 x 6.81 x 4.56 [224 x 173 x 116]	9	PDF
SCE-12PBGX	\$137.00	10.69 x 6.56 x 4.56 [272 x 167 x 116]	12	PDF

Note: Dimensions in inches [millimeters].

NEMA 4, 12, and 13 22mm Wall-Mount Pushbutton



Dimensions

