



## Main

Range of Product	Harmony 9001B
Product or Component Type	Complete control station
Device short name	9001BR
Control station application	Stop function
Colour of base of enclosure	Grey

## Complementary

Material	Cast zinc
Marking	CE
Type of operator	momentary
Control station composition	1 push-button, red, white STOP
Contacts type and composition	1 NC
Mechanical durability	5000000 cycles
[Ie] rated operational current	5 A 600 V, AC
Device mounting	Surface
Type of Installation	Indoor

## Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
NEMA degree of protection	NEMA 7/9
Product Certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Environmental characteristic	Hazardous location

## Ordering and shipping details

Category	21421 - 9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	785901600855
Nbr. of units in pkg.	1
Package weight(Lbs)	3.54 lb(US) (1.606 kg)
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	13.97 in (35.484 cm)
Package 1 width	5.50 in (13.97 cm)
Package 1 Length	35.48 in (90.129 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------