



### Main

Range of Product	Harmony 9001BW
Product or Component Type	Complete control station
Device short name	9001BW
Control station application	Two functions
Colour of base of enclosure	Grey

### Complementary

Material	Cast aluminium
Cable entry	1 entry for 1/2" - 14 NPT
CAD overall width	2.76 in (70 mm)
CAD overall height	4.25 in (108 mm)
CAD overall depth	3.58 in (91 mm)
Type of operator	maintained
Control station composition	1 flush push-button, black, white ON 1 flush push-button, black, white OFF
Contacts type and composition	1 NO + 1 NC
Contact operation	Interlocked
Mechanical durability	5000000 cycles
[Ie] rated operational current	0.6 A 600 V, AC-1/DC-1 0.75 A 480 V, AC 1.5 A 240 V, AC 3.75 A 120 V, AC
Device mounting	Surface
Type of Installation	Indoor/outdoor

### Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
NEMA degree of protection	NEMA 1 NEMA 4
Standards	UL 508 EN/IEC 60947-5-5 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-4 JIS C 4520 EN/IEC 60947-5-1
Product Certifications	UL Listed CSA
Environmental characteristic	Waterproof Dustproof

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	21421 - 9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	785901857747
Nbr. of units in pkg.	1
Package weight(Lbs)	2.50 lb(US) (1.134 kg)
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	8.89 in (22.581 cm)
Package 1 width	3.50 in (8.89 cm)
Package 1 Length	22.58 in (57.355 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------