



Main

| | |
|---------------------------|---------------|
| Range of Product | Harmony 9001K |
| Product or Component Type | Contact block |
| Device short name | K |

Complementary

| | |
|--------------------------|-------------------------|
| Contact operation | Series G style |
| Short-circuit protection | 10 A without fingersafe |

Environment

| | |
|------------------------|--|
| Product Certifications | UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE |
|------------------------|--|

Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 21434 - 9001 KA CONTACT BLOCKS |
| Discount Schedule | CS1 |
| GTIN | 785901028789 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.96 oz (27.2 g) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------|-------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.98 in (2.5 cm) |
| Package 1 width | 4.02 in (10.2 cm) |
| Package 1 Length | 5.98 in (15.2 cm) |

Offer Sustainability

| | |
|---------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |

| | |
|----------------------------|--|
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|