



Main

Range of Product	Harmony 9001K
Product or Component Type	Mushroom head push-button
Device short name	K
Type of operator	Spring return
Operator profile	Green mushroom Ø 57 mm
Operator additional information	Screw-in with set screw security

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Light source	without
Light source	Without
Light block supply	Without supply
Contacts type and composition	1 NC
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

Environment

Product Certifications	CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR NEMA CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	NULL
Nbr. of units in pkg.	1
Package weight(Lbs)	8.00 oz (226.796 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.43 in (29.032 cm)
Package 1 width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------