



Overview

Lead time	Usually in Stock
-----------	------------------



General

Provided Equipment	User Manual Rack Mounting brackets
--------------------	---------------------------------------

Physical

Cable length	12 ft (3.66 m)
Color	Black
Depth	2.24 in (5.7 cm)
Height	1.73 in (4.4 cm)
Net Weight	5.51 lb(US) (2.5 kg)
Width	17.60 in (44.7 cm)

Input

Line Rated Current	24 A
Permissible voltage	90...132 V
Max line current	24 A
Input current limits	30 A
Load Capacity	2880 VA
Input Frequency	50/60 Hz
Plug standard	NEMA L5-30P
Nominal Input Voltage	100 V 120 V

Output

Number of power socket outlets	10 NEMA 5-20R
--------------------------------	---------------

Conformance

Product Certifications	CUL Listed UL Listed
Standards	UL 60950

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient air temperature for operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304192930
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	IN

Packing Units

Package 1 Height	5.98 in (15.2 cm)
Package 1 width	19.13 in (48.6 cm)
Package 1 Length	6.97 in (17.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------