


Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Accessory / separate part category	Protection accessory
Product or component type	Current limiting module
Function of module	Increasing the breaking capacity of a circuit breaker
Range compatibility	TeSys GV2
Product compatibility	GV2RT GV2ME GV2P GV2L
Mounting location	On top of the circuit breaker
[Ie] rated operational current	32 A
[Ith] conventional free air thermal current	63 A IEC 60947-1
Operating threshold	1500 A
Breaking capacity	<= 100 kA depending on protective device
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ui] rated insulation voltage	690 V AC 50/60 Hz IEC 60947-1

Complementary

Connections - terminals	Screw clamp terminals 1 x 0.00...0.04 in ² (1.5...25 mm ²) rigid Screw clamp terminals 2 x 0.00...0.02 in ² (1.5...10 mm ²) rigid Screw clamp terminals 1 x 0.00...0.04 in ² (1.5...25 mm ²) flexible without cable end Screw clamp terminals 2 x 0.00...0.02 in ² (1.5...10 mm ²) flexible without cable end Screw clamp terminals 1 x 0.00...0.02 in ² (1.5...16 mm ²) flexible with cable end Screw clamp terminals 2 x 0.00...0.01 in ² (1.5...4 mm ²) flexible with cable end
Tightening torque	19.47 lbf.in (2.2 N.m)
Net weight	0.29 lb(US) (0.13 kg)

Ordering and shipping details

Category	22366 - MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	00785901209959
Package weight(Lbs)	0.12 kg (0.27 lb(US))
Returnability	Yes
Country of origin	FR

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Current Limiter

GV1L3

