



Product availability: Stock - Normally stocked in distribution facility



### Main

Range	TeSys
Product or component type	Enclosure
Device short name	GV2MP
Accessory / separate part category	Mounting accessory
Product compatibility	GV2ME
Enclosure type	Flush mounting

### Complementary

Auxiliary mounting location	Right Left
Height	5.51 in (140 mm)
Width	4.19 in (106.5 mm)
Depth	3.27 in (83 mm)
Net weight	0.29 lb(US) (0.13 kg)

### Environment

IP degree of protection	IP55 front face
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901832720
Package weight(Lbs)	0.24 kg (0.53 lb(US))
Returnability	Yes
Country of origin	CZ

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------