


CODE (1)	AUX. CONTACTS		TYPE OF CONNECTION
	NO	NC	
40	4	—	SCREW CLAMP
31	3	1	
22	2	2	
13	1	3	
04	—	4	

Block of 4 contacts cannot be used with LP4-K or LP5-K contactors.

TYPE OF CABLE	WIRE SIZE
STANDARD CABLE WITHOUT CABLE END	AWG 16-10
STANDARD CABLE WITH CABLE END	AWG 18-10
SOLID CABLE	AWG 22-12



Catalog Number: LA1 KN(1)
 Ratings: —
 UL File/Guide: —
 CSA File/Guide: —
 Meets Standards: —
 Weight: —
 Wire Size: SEE CHART
 Terminal torque: 7 LB-IN
 Mounting Hwd.: CLIP-ON FRONT MOUNTING

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

DO NOT SCALE DRAWING
 UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE
PROJECTION

TOLERANCES

UNLESS OTHERWISE SPECIFIED
2 PLACE DECIMALS ± .01

IEC CONTACT BLOCK (K-LINE)
 LA1 KN(1)



DWG# E0210801-01
 NO.