



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	LP1D80 LP1D400...D650 LC1D80...D95 LC1D400...D650

Complementary

Mounting mode	By screws
Suppressor technology	Bidirectional peak limiting diode
[Uc] control circuit voltage	24 V DC
Maximum peak voltage	2 Uc
Product weight	0.04 lb(US) (0.018 kg)

Environment

ambient air temperature for operation	-13...131 °F (-25...55 °C)
ambient air temperature for storage	-40...176 °F (-40...80 °C)

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.