



Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Device short name	LA4SK
Product or component type	Suppressor module
Product compatibility	CA2SK LC1SK06 CA3SK LC1SKGC LP1SK06
Suppressor technology	Varistor (peak limiting)
Quantity per set	Set of 10

Complementary

Mounting location	Right hand side
[Uc] control circuit voltage	24...48 V AC 24...48 V DC
Maximum peak voltage	2 Uc
Net weight	0.01 lb(US) (0.003 kg)

Environment

Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Ambient air temperature for storage	-58...158 °F (-50...70 °C)

Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
GTIN	00785901866800
Package weight(Lbs)	0.00 kg (0.01 lb(US))
Returnability	Yes
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty

18 months
