



Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Switch module
Quantity per Set	Set of 3

Complementary

Product Compatibility	LC1G265...330
Accessory / Separate Part Type	Kit
Maximum [Ie] rated operational current	440 A AC-1 <= 440 V 104 °F (40 °C) 330 A AC-3 <= 440 V 104 °F (40 °C)
Poles description	3P
Connections - Terminals	Bolted connection

Environment

Pollution degree	3 IEC 60947-1
Operating altitude	9842.52 ft (3000 m) without power derating 5000 m with derating factor
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048.4
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)

Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	03606481916747
Returnability	Yes

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.69 in (17.0 cm)
Package 1 Width	10.24 in (26.0 cm)
Package 1 Length	6.30 in (16.0 cm)
Package 1 Weight	7.72 lb(US) (3.5 kg)
Unit Type of Package 2	S03
Number of Units in Package 2	3
Package 2 Height	11.81 in (30.0 cm)

Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	24.47 lb(US) (11.1 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product