



## Main

|                           |                                |
|---------------------------|--------------------------------|
| Range                     | TeSys                          |
| Device short name         | LAD4                           |
| Product or component type | Suppressor module              |
| Product compatibility     | LC1D09...D38<br>LC1DT20...DT40 |

## Complementary

|                              |                        |
|------------------------------|------------------------|
| Mounting location            | Side                   |
| Mounting mode                | By clips               |
| Suppressor technology        | RC circuit             |
| [Uc] control circuit voltage | 24...48 V AC <= 400 Hz |
| Maximum peak voltage         | 3 Uc                   |
| Product weight               | 0.03 lb(US) (0.012 kg) |

## Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| ambient air temperature for operation | -13...131 °F (-25...55 °C) |
| ambient air temperature for storage   | -40...176 °F (-40...80 °C) |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.