



Main

Range	TeSys
Device short name	LT6CT
Product or Component Type	Current transformer
Range compatibility	TeSys T motor controller

Complementary

Current transformer ratio	200/1
Accuracy class	Class 5P
Precision limit factor	15
[Ui] rated insulation voltage	690 V
Diameter	0.39 in (10 mm)
Cable cross section	0.47 in ² (300 mm ²)
Height	4.21 in (107 mm)
Width	3.74 in (95 mm)
Depth	0.98 in (25 mm)
Net Weight	1.21 lb(US) (0.55 kg)

Environment

Standards	BS 7626 IEC 60185
Maximum ambient air temperature for operation	122 °F (50 °C)

Ordering and shipping details

Category	22338 - SOLID STATE OVERLOAD RELAYS
Discount Schedule	I12
GTIN	3389119405348
Nbr. of units in pkg.	1
Package weight(Lbs)	16.16 oz (458 g)
Returnability	No
Country of origin	GB

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	4.92 in (12.5 cm)
Package 1 Length	4.17 in (10.6 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Weight	20.21 lb(US) (9.167 kg)

Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------