



## Main

Range	TeSys
Device short name	LT6CT
Product or Component Type	Current transformer
Range compatibility	TeSys T motor controller

## Complementary

Current transformer ratio	400/1
Accuracy class	Class 5P
Precision limit factor	15
[Ui] rated insulation voltage	690 V
Diameter	0.39 in (10 mm)
Cable cross section	0.47 in <sup>2</sup> (300 mm <sup>2</sup> )
Height	4.21 in (107 mm)
Width	3.74 in (95 mm)
Depth	0.98 in (25 mm)
Net Weight	1.21 lb(US) (0.55 kg)

## Environment

Standards	BS 7626 IEC 60185
Maximum ambient air temperature for operation	122 °F (50 °C)

## Ordering and shipping details

Category	22338 - SOLID STATE OVERLOAD RELAYS
Discount Schedule	I12
GTIN	3389110943276
Nbr. of units in pkg.	1
Package weight(Lbs)	14.53 oz (412 g)
Returnability	No
Country of origin	GB

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.26 in (3.2 cm)
Package 1 width	4.80 in (12.2 cm)
Package 1 Length	4.02 in (10.2 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Weight	20.03 lb(US) (9.084 kg)

Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------