

# Product data sheet

## Characteristics

# VLS8C2

Disconnect switch, TeSys VLS, interlock for line changeover (I-0-II), size 2, 30A to 125A devices



### Main

Range	TeSys
Product or Component Type	Mechanical interlock
Accessory / separate part category	Interlocking accessory
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 padlock 0.16 in (4 mm)
Marking	1 - 0 - 2

### Complementary

Fixing Mode	By clips and screws
Tightening torque	4.43 lbf.in (0.5 N.m)
Height	1.77 in (45 mm)
Width	5.51 in (140 mm)
Depth	1.06 in (27 mm)
Net Weight	0.17 lb(US) (0.075 kg)

### Environment

Standards	UL98 CSA C22.2 No 4
Product Certifications	CULus EAC
IP Degree of Protection	IP20

### Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	3606481156860
Nbr. of units in pkg.	1
Package weight(Lbs)	3.84 oz (109 g)
Returnability	Yes
Country of origin	IT

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.05 in (5.2 cm)
Package 1 width	2.87 in (7.3 cm)
Package 1 Length	5.67 in (14.4 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	35
Package 2 Weight	9.98 lb(US) (4.528 kg)
Package 2 Height	11.81 in (30 cm)

Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>