



## Main

Range of product	Altivar
Accessory / separate part category	Connection accessory
Accessory / separate part type	Remote cable
Product compatibility	VW3M1701 VW3A1101
Accessory / separate part destination	Remote graphic display terminal
Range compatibility	Altivar 61 Altistart 22 Altivar 12 Altivar 212 Altivar 71 Altivar Machine ATV340 Altivar 32 Altivar 71Q Altivar 312 Easy Altivar 610 Altivar 61Q Altivar Process ATV600 Altivar Machine ATV320 Easy Altivar 310 Altivar 312 Solar Lexium 32 Altivar Process ATV900
Cable length	3.28 ft (1 m)

## Complementary

Electrical connection	2 male connectors
Connector type	RJ45
Net Weight	0.11 lb(US) (0.05 kg)

## Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	00785901806967
Nbr. of units in pkg.	1
Package weight(Lbs)	0.12 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	CN

## Packing Units

Package 1 Height	0.200 dm
Package 1 width	1.300 dm
Package 1 Length	1.300 dm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------