



Main

Product or component type	Ferrite suppressors for downstream contactor opening
Range compatibility	Altivar 312 Altivar 312 Solar Altivar 12
Product specific application	Output filter
Compatibility with variable speed drives	Variable speed drive ATV12H 0.55 kW, 200...240 V, single phase Variable speed drive ATV12H 0.75 kW, 200...240 V, single phase Variable speed drive ATV12H 1.5 kW, 200...240 V, single phase Variable speed drive ATV12H 2.2 kW, 200...240 V, single phase Variable speed drive ATV12H 0.75 kW, 200...240 V, three phase Variable speed drive ATV12H 1.5 kW, 200...240 V, three phase Variable speed drive ATV12H 2.2 kW, 200...240 V, three phase Variable speed drive ATV312 0.55 kW, 200...240 V, single phase Variable speed drive ATV312 0.75 kW, 200...240 V, single phase Variable speed drive ATV312 1.1 kW, 200...240 V, single phase Variable speed drive ATV312 1.5 kW, 200...240 V, single phase Variable speed drive ATV312 2.2 kW, 200...240 V, single phase Variable speed drive ATV312 0.55 kW, 200...240 V, three phase Variable speed drive ATV312 0.75 kW, 200...240 V, three phase Variable speed drive ATV312 1.1 kW, 200...240 V, three phase Variable speed drive ATV312 1.5 kW, 200...240 V, three phase Variable speed drive ATV312 2.2 kW, 200...240 V, three phase
Sale per indivisible quantity	3

Ordering and shipping details

Category	22042 - ATV12 DRIVE AND ACCESSORIES
Discount Schedule	CP4B
GTIN	00785901583950
Nbr. of units in pkg.	1
Package weight(Lbs)	0.34 lb(US) (0.15 kg)
Returnability	No
Country of origin	FR

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.13 in (10.5 cm)
Package 1 width	5.51 in (14 cm)
Package 1 Length	6.30 in (16 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Weight	3.56 lb(US) (1.613 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	56
Package 3 Weight	48.16 lb(US) (21.844 kg)
Package 3 Height	31.50 in (80 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------