



Main

Range of product	Altivar
Accessory / separate part category	Mounting and fixing accessories
Accessory / separate part type	Mounting plate
Product compatibility	ATV12HU15M2 ATV12H075F1 ATV12HU15M3 ATV12HU22M2 ATV12HU22M3 ATV312H037N4 ATV312H055N4 ATV312H075N4 ATV312H075S6 ATV312HU11M2 ATV312HU11M3 ATV312HU11N4 ATV312HU15M2 ATV312HU15M3 ATV312HU15N4 ATV312HU15S6 ATV312HU22M3 Variable speed drive ATV320...C 1.1 kW, 200...240 V, single phase Variable speed drive ATV320...C 1.5 kW, 200...240 V, single phase Variable speed drive ATV320...C 2.2 kW, 200...240 V, single phase Variable speed drive ATV320...C 0.37 kW, 380...500 V, three phase Variable speed drive ATV320...C 0.55 kW, 380...500 V, three phase Variable speed drive ATV320...C 0.75 kW, 380...500 V, three phase Variable speed drive ATV320...C 1.1 kW, 380...500 V, three phase Variable speed drive ATV320...C 1.5 kW, 380...500 V, three phase Variable speed drive ATV320...C 0.75 kW, 525...600 V, three phase Variable speed drive ATV320...C 1.5 kW, 525...600 V, three phase
Accessory / separate part destination	Variable speed drive
Range compatibility	Altivar 312 Altivar 12 Altivar 312 Solar Altivar Machine ATV320

Complementary

Mounting support	35 mm symmetrical DIN rail
Net Weight	0.85 lb(US) (0.385 kg)

Ordering and shipping details

Category	22042 - ATV12 DRIVE AND ACCESSORIES
Discount Schedule	CP4B
GTIN	00785901980773
Nbr. of units in pkg.	1
Package weight(Lbs)	0.84 lb(US) (0.38 kg)

Returnability	Yes
Country of origin	JP

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.83 in (7.2 cm)
Package 1 width	9.06 in (23 cm)
Package 1 Length	6.85 in (17.4 cm)
Unit Type of Package 2	S06
Number of Units in Package 2	50
Package 2 Weight	71.43 lb(US) (32.4 kg)
Package 2 Height	28.94 in (73.5 cm)
Package 2 width	23.62 in (60 cm)
Package 2 Length	31.50 in (80 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

