



SIMATIC ET 200SP, BusAdapter BA 2xRJ45, 2 RJ45 sockets

General information			
Product type designation		BA 2x RJ45	
Interfaces			
Number of PROFINET interfaces		1; 2 ports (switch) 2x RJ45	
Supports protocol for PROFINET IO			
● Number of RJ45 ports		2	
Cable length			
— Cu conductors		100 m	
Standards, approvals, certificates			
Ecological footprint			
● environmental product declaration		Yes	
Global warming potential			
— global warming potential, (total) [CO2 eq]		1.14 kg	
— global warming potential, (during production) [CO2 eq]		1.2 kg	
— global warming potential, (during operation) [CO2 eq]		0 kg	
— global warming potential, (after end of life cycle) [CO2 eq]		-0.069 kg	
Ambient conditions			
Ambient temperature during operation			
● horizontal installation, min.		-30 °C	
● horizontal installation, max.		60 °C	
● vertical installation, min.		-30 °C	
● vertical installation, max.		50 °C	
Altitude during operation relating to sea level			
● Installation altitude above sea level, max.		5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual	
Absolute humidity			
● dew point, min.		-60 °C; suitable for dry room applications	
Dimensions			
Width		20 mm	
Height		69.5 mm	
Depth		59 mm	
Weights			
Weight, approx.		46 g	
Classifications			
		Version	Classification
eClass		16	27-24-26-92

eClass	14	27-24-26-92
eClass	12	27-24-26-92
eClass	9.1	27-24-26-92
eClass	9	27-24-26-92
eClass	8	27-24-26-92
eClass	7.1	27-24-26-92
eClass	6	27-24-26-92
ETIM	10	EC002584
ETIM	9	EC002584
ETIM	8	EC002584
ETIM	7	EC002584
IDEA	4	3552
UNSPSC	15	32-15-17-03

Approvals / Certificates	
General Product Approval	EMV

CCC

EAC

CE
EG-Konf.

UK
CA

[Confirmation](#)

RCM

Test Certificates	other	Environment		
Miscellaneous		Confirmation	Environmental Con- firmations	Environmental Con- firmations

last modified:

2/1/2026 