

## CODE NUMBER

3315329BT

## DESCRIPTION

Bluetooth, 4" Trim Plate, Battery Power Supply, Below Deck  
Thermostatic Mixing Valve, Polished Chrome Finish, 0.35 gpm, Multi-  
Laminar Spray, Infrared Sensor, Optima® Battery or Turbine-Powered  
Deck-Mounted Mid Body Faucet.

## DETAILS

- Flow Rate: 0.35 gpm (1.3 Lpm) (0.35GPM)
- Spray Type: Multi-Laminar (MLM)
- Sensor Type: Infrared
- Mounting Type: Single Hole
- Mounting Size: Single Hole 1-1/4" to 1-1/2"
- Trim Plate: 4" (102mm) (4)
- Power Supply: Battery (BAT)
- Temperature Mixer: Below Deck Thermostatic Mixing Valve (BDT)
- Finish: Polished Chrome (CP)
- Factory Default Timeout: 30 seconds
- Factory Default Gallons per Cycle: 0.175

## FEATURES

ADA Compliant, Water Usage and Battery Strength Reporting,  
Wireless Settings Adjustment, Commercial Grade Faucet, Integrated  
Water Shut-off, Hygienic Line Flush, On-demand or Metered  
Activation, Self-adapting Sensor, Cast Brass Spout, Quick Connect  
Fittings

## ELECTRICAL SPECIFICATIONS

- Battery Life: 3 years 8,000 cycles/month
  - Optional power harvesting significantly extends service life
- Sensor Range: 4" - 5" (102 - 127mm)
- Timeout Adjustment Settings: 30s

## POWER SUPPLY OPTIONS

- 6VDC Plug Adapter (sold separately), 0362006\*
- 6VDC Ganged Adapter Kit (up to 6 units)(sold separately), 0362035\*
- 24VAC Box Transformer (up to 3 units)(sold separately), 0345370PK\*
- Optional Turbine Energy Harvesting

\* when converting units to hardwired with battery back-up

## VIDEOS


- ▶ Sloan Connect App®
- ▶ Sloan Optima Below Deck Faucet

## DOWNLOADS

- [Optima Smart Faucet Below Deck Installation Instructions](#)
- [ETF-80/880 and EBF-85/187 Below Deck Repair and Maintenance Guide](#)
- [Faucet Spray Heads Repair and Maintenance Guide](#)



Variation not shown: 4" Trim Plate



## COMPLIANCES & CERTIFICATIONS



(ADA Compliant, ASME A112.18.1 Compliant, ASSE 1070,  
CalGreen Compliant, CEC Compliant, cUPC Certified, cUPC Low  
Lead Compliant, EPD, HPD, IAPMO, LEED V4 Water Efficiency  
Credit, NSF-61, NYC604.4, Proposition 65, Satisfies LEED  
Credits, TAS, UPC Certified, UPC Low Lead Compliant,  
WaterSense Listed, WELL Building Standard)

## RECOMMENDED SPECIFICATION

Faucet shall include cast brass body, quick-connect fittings,  
twist-off/shut-off solenoid assembly, removable battery  
cartridge, flexible power supply and allow adjustment of  
settings wirelessly via Apple or Android smartphones.

## NOTES

All information contained within this document subject to  
change without notice.

Looking for other variations of the EBF-85 product? [View the](#)

Sloan 10500 Seymour Ave, Franklin Park, IL 60131

Phone: 800.982.5839 • Fax: 800.447.8329 • [sloan.com](http://sloan.com)

- [Trim Plate Guide](#)
- [Additional Downloads](#)

[general spec sheet with all options.](#)

[Find a matching soap dispenser](#) for this faucet.

[Find a compatible sink](#) for this faucet.

**WARRANTY**

[View Warranty Information](#)

**ROUGH-IN**

