



1

# ATyS M

Motorised and  
from 40 to 160

## References

### ATyS M 3s

#### Rating (A)

40 A

63 A

80 A

100 A

125 A

160 A

(1) For the three-phase version

(2) 1 NO/NC contact block

### ATyS M 6s

#### Rating (A)

40 A

63 A

#### No. of