

Accessories Dimensions

Handles


[inches/mm]



Direct Handle for UL 98 Compact Non-Fusible Disconnect Switches

22995032

Handle Dimensions



External Handles for UL 98 Compact Non-Fusible Disconnect Switches

S00 Type

Handle Dimensions	Direction of Operation	Door Drilling

S0 Type

Handle Dimensions	Direction of Operation	Door Drilling

S01 Type

Handle Dimensions	Direction of Operation	Door Drilling

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]



Direct Handles for UL 98 Non-Fusible Disconnect Switches	
26995052	37996012
Handle Dimensions	Handle Dimensions

External Handles for UL 98 Non-Fusible Disconnect Switches		
S2 Type		
Handle Dimensions	Direction of Operation	Door Drilling
S3 Type		
Handle Dimensions	Direction of Operation	Door Drilling

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles


[inches/mm]



Direct Handle for UL 508 Non-Fusible Disconnect Switches

22995012

Handle Dimensions



External Handles for UL 508 Non-Fusible Disconnect Switches

S00 Type

Handle Dimensions	Direction of Operation	Door Drilling

S0 Type

Handle Dimensions	Direction of Operation	Door Drilling

S01 Type



Handle Dimensions	Direction of Operation	Door Drilling

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]



Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]



Direct Handles for UL 489 Compact Fusible Disconnect Switches

26995052	37996012
Handle Dimensions	Handle Dimensions

External Handles for UL 489 Compact Fusible Disconnect Switches

S0 Type		
Handle Dimensions	Direction of Operation	Door Drilling
3.07 [78.0] 3.46 [88.0] 1.46 [37.0]	90°	4X 0.27 [7.0] 1.22 [31.0] 1.10 [28.0] 1.57 [40.0] 0.53 [13.5] 0.12 [3.0] 0.89 [22.5]
S1 Type		
Handle Dimensions	Direction of Operation	Door Drilling
3.07 [78.0] 2.76 [70.0] 1.73 [44.0]	90° 65° TEST TEST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES	0.27 [7.0] 1.46 [37.0] 1.57 [40.0] 1.10 [28.0] 1.46 [37.0]



Note: Test position included on certain models only as indicated in the selection tables.

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]

Direct Handles for UL 98 Fusible Disconnect Switches	
36297910	38596011
Handle Dimensions	Handle Dimensions
	

External Handles for UL 98 Fusible Disconnect Switches

S1 Type			
Handle Dimensions	Direction of Operation		Door Drilling
	EST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES		
S2 Type			
Handle Dimensions	Direction of Operation		Door Drilling
	EST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES		
S3 Type			
Handle Dimensions	Direction of Operation		Door Drilling
	EST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES		





Note: Test position included on certain models only as indicated in the selection tables.

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions


Shafts for Non-Fusible Disconnect Switches

[inches/mm]

Shafts for Non-Fusible Disconnect Switches				
Shafts for S00, S0 Handle Type	Part Number	Switch Body Rating (A)	Length	
			in	mm
	14070515	16 - 100	5.9	150
	14070520		7.9	200
	14070532		12.6	320
Shafts for S01 Handle Type	Part Number	Switch Body Rating (A)	Length	
			in	mm
	14040520	16 - 100	7.9	200
	14040532		12.6	320
	14040540		15.7	400
Shafts for S1, S2 Handle Type	Part Number	Switch Body Rating (A)	Length	
			in	mm
	14001020	100 - 400	7.9	200
	14001032		12.6	320
	14001040		15.7	400
Shafts for S3 Handle Type	Part Number	Switch Body Rating (A)	Length	
			in	mm
	14011520	600	7.9	200
	14011532		12.6	320
	14011540		15.7	400

Please see our website www.AutomationDirect.com for complete engineering drawings.





Shaft Length Minimum Dimensions						
Use standard lengths: 7.9 in / 200mm – 12.6 in / 320mm – 15.7 in / 400mm						
Switch Body Rating (A)	Dimension X		Handle Type	Length		Part Number
	in	mm		in	mm	
100 - 400	5.31 - 10.43	135 - 265	S2	7.9	200	14001020
100 - 400	5.31 - 15.16	135 - 385	S2	12.6	320	14001032
100 - 400	5.31 - 18.31	135 - 465	S2	15.7	400	14001040
600	8.70 - 13.50	221 - 343	S3	7.9	200	14011520
600	8.70 - 18.23	221 - 463	S3	12.6	320	14011532
600	8.70 - 21.38	221 - 543	S3	15.7	400	14011540



Accessories Dimensions


Shafts for Fusible Disconnect Switches

[inches/mm]

Shafts for Fusible Disconnect Switches									
Shafts for S0 Handle Type	Part Number	Body Switch Rating	Length		Shafts for S2 Handle Type	Part Number	Body Switch Rating	Length	
			in	mm				in	mm
	14050620	30A	7.9	200		14001020	30A to 400A	7.9	200
	14050632		12.6	320		14001032	30A to 200A	12.6	320
	14050640		15.7	400		14001040	30A to 400A	15.7	400
Shafts for S1 Handle Type	Part Number	Switch Body Rating	Length		Shafts for S3 Handle Type	Part Number	Switch Body Rating	Length	
			in	mm				in	mm
	14010520	30A	7.9	200		14001220	600A	7.9	200
	14010532		12.6	320		14001232		12.6	320
	14010540		15.7	400		14001240		15.7	400

Please see our website www.AutomationDirect.com for complete engineering drawings.

Shaft Length Minimum Dimensions						
Use standard lengths: - 7.9 in / 200mm - 12.6 in / 320mm - 15.7 in / 400mm						
Switch Body Rating (A)	Dimension X		Handle Type	Length		Part Number
	in	mm		in	mm	
30	4.02 - 9.65	102 - 245	S0	7.9	200	14050620
30	4.02 - 14.37	102 - 365	S0	12.6	320	14050632
30	4.02 - 17.52	102 - 445	S0	15.7	400	14050640
30	4.02 - 9.65	102 - 245	S1	7.9	200	14010520
30	4.02 - 14.37	102 - 365	S1	12.6	320	14010532
30	4.02 - 17.52	102 - 445	S1	15.7	400	14010540
30 - 100	5.3 - 9.06	135 - 230	S2	7.9	200	14001020
200	5.7 - 9.06	145 - 230	S2	7.9	200	14001020
400	7.87 - 10.24	200 - 260	S2	7.9	200	14001020
30 - 100	5.3 - 13.78	135 - 350	S1, S2	12.6	320	14001032
200	5.7 - 13.78	145 - 350	S2	12.6	320	14001032
400	7.87 - 14.96	200 - 380	S2	12.6	320	14001032
30 - 100	5.3 - 16.93	135 - 430	S1, S2	15.7	400	14001040
200	5.7 - 16.93	145 - 430	S2	15.7	400	14001040
400	7.87 - 18.1	200 - 460	S2	15.7	400	14001040
600 - 800	10.63 - 11.97	270 - 304	S3	7.9	200	14001220
600 - 800	10.63 - 16.69	270 - 424	S3	12.6	320	14001232
600 - 800	10.63 - 19.84	270 - 504	S3	15.7	400	14001240




Accessories Dimensions




Lugs


[inches/mm]




39542020, 39543020, 39544020



39543040



39543041




39543060

Please see our website www.AutomationDirect.com for complete engineering drawings.


Accessories Dimensions

Auxiliary Contacts and Additional Poles




[inches/mm]






27990021
27990022
27990121






22990001
22990011
39990701
39990702






22001000
22001001
22001002
22001003
22001004




3999U041
3999U042



22011003
22011006
22001010
22005011
22009011



22696009



Please see our website www.AutomationDirect.com for complete engineering drawings.