

SIRCO AC - References

Heavy duty applications - Front operation 3 & 4 pole

Rating (A)	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	Auxiliary contact	Terminal shrouds	Terminal screens
200 A	3 P	26AC 3020	J1 type Black 1112 1111 ⁽¹⁾ J1 type Red 1113 1111	S2 type Black IP65 1421 2111 ⁽¹⁾ Black IP65 1423 2111 Red IP65 1424 2111	200 mm 1400 1020 320 mm 1400 1032 ⁽¹⁾ 500 mm 1400 1050		3P 2694 3021 ⁽²⁾⁽³⁾ 4 P 2694 4021 ⁽²⁾⁽³⁾	3P 2698 3020 ⁽³⁾ 4 P 2698 4020 ⁽³⁾
	4 P	26AC 4020						
250 A	3 P	26AC 3025						
	4 P	26AC 4025						
315 A	3 P	26AC 3031						
	4 P	26AC 4031						
400 A	3 P	26AC 3040						
	4 P	26AC 4040						
500 A	3 P	26AC 3050						
	4 P	26AC 4050						
CD 630 A	3 P	26AC 3063						
	4 P	26AC 4063						
630 A	3 P	26AC 3064	J4 type Black 1142 1111 ⁽¹⁾ Red 1143 1111	S4 type Black IP65 1443 3111 ⁽¹⁾ Red IP65 1444 3111	200 mm 1401 1520 320 mm 1401 1532 ⁽¹⁾ 400 mm 1401 1540	1 st contact NO/NC 2699 0031 2 nd contact NO/NC 2699 0032	3P 2694 3051 ⁽²⁾⁽³⁾ 4 P 2694 4051 ⁽²⁾⁽³⁾	3P 2698 3050 ⁽³⁾ 4 P 2698 4050 ⁽³⁾
	4 P	26AC 4064						
800 A	3 P	26AC 3080						
	4 P	26AC 4080						
1000 A	3 P	26AC 3100						
	4 P	26AC 4100						
CD 1250 A	3 P	26AC 3120						
	4 P	26AC 4120						
1250 A	3 P	26AC 3121						
	4 P	26AC 4121						
1600 A	3 P	26AC 3160						
	4 P	26AC 4160						
2000 A	3 P	26AC 3200	S5 type Black 2799 7042 ⁽¹⁾ Red 2799 7043	S5 type Black IP65 1453 8111 ⁽¹⁾ Red IP65 1454 8111	200 mm 2799 3015 320 mm 2799 3018 ⁽¹⁾ 450 mm 2799 3019		3P 2698 3200 ⁽²⁾⁽³⁾ 4 P 2698 4200 ⁽²⁾⁽³⁾	
	4 P	26AC 4200						
4000 A	3 P	26AC 3400	V0 type Black 2799 7072 ⁽¹⁾	V0 type Black 2799 7155 ⁽¹⁾		1 st / 2 nd included	3/4P 1509 4200 ⁽⁴⁾	
	4 P	26AC 4400						

(1) Standard.

(2) Mandatory for voltage greater than 415 VAC.

(3) Top or bottom.

(4) Top and bottom.