

References (continued)

Single PV circuit 1000 VDC - Back plate mounting

Rating (A)	Circuit type	Number of poles of the device	Number of pole(s) in series per polarity	Switch body	Direct handle ⁽²⁾	External handle	Shaft for external handle	Bridging bars		
100 A	Single PV circuit	4 P	2 P+, 2 P-	26PV 4010	J1 type Black 1112 1111 ⁽¹⁾ Red 1113 1111	S2 type Black IP55 1421 2111 ⁽¹⁾ Black IP65 1423 2111 Red IP65 1424 2111	200 mm 1400 1020 320 mm 1400 1032 ⁽¹⁾ 500 mm 1400 1050	2609 2025		
125 A				26PV 4012						
160 A				26PV 4016						
200 A				26PV 4020						
250 A				26PV 4025						
315 A				26PV 4031						
400 A				26PV 4040						
500 A				26PV 4050						
630 A				26PV 4063						
800 A				26PV 4080						
1000 A				26PV 4100						
1250 A				26PV 4120	J4 type Black 1142 1111 ⁽¹⁾ Red 1143 1111	S4 type Black IP65 1443 3111 ⁽¹⁾ Red IP65 1444 3111	200 mm 1401 1520 320 mm 1401 1532 ⁽¹⁾ 400 mm 1401 1540	2 x 2609 1100		
1600 A				26PV 4160	2 x 2609 1160					
2000 A				26PV 4200	2 x 26091200					
2500 A										
3200 A						Please consult us	-	-	-	-

(1) Standard.

(2) Other types of operation handle available. see "Accessories" pages.

Dual PV circuit 1000 VDC - Back plate mounting

Rating (A)	Circuit type	Number of poles of the device	Number of pole(s) in series per polarity	Switch body	Direct handle ⁽²⁾	External handle	Shaft for external handle	Bridging bars
100 A	Dual PV circuit	8 P	2x (2P+, 2P-)	26PV 8010	J3 type Black 1132 1111 ⁽¹⁾ Red 1133 1111	S3 type Black IP55 1431 3111 ⁽¹⁾ Black IP65 1433 3111 Red IP65 1434 3111	200 mm 1401 1520 320 mm 1401 1532 ⁽¹⁾ 400 mm 1401 1540	2 x 2609 2025
125 A				26PV 8012				
160 A				26PV 8016				
200 A				26PV 8020				
250 A				26PV 8025				
315 A				26PV 8031				
400 A				26PV 8041				
500 A				26PV 8051				
630 A				26PV 8063				
800 A				Please consult us				
1000 A				26PV 8100	J4 type Black 1142 1111 ⁽¹⁾ Red 1143 1111	S4 type Black IP65 1443 3111 ⁽¹⁾ Red IP65 1444 3111	200 mm 2799 3015 320 mm 2799 3018 ⁽¹⁾ 450 mm 2799 3019	4 x 2609 1100
1250 A				26PV 8120	4 x 2609 1200			
1600 A				26PV 8160	V1 type Black 2799 7074	S5 type Black IP65 1453 8111 Red IP65 1454 8111		
2000 A				26PV 8200				

(1) Standard.

(2) Other types of operation handle available. see "Accessories" pages.