

References

Front operation

Rating (A)	No. of poles	Switch body Direct operation	Switch body External operation	Direct handle	External handle	Shaft for external handle	Auxiliary contact				
ND 125 A	3 P	2915 3012	2921 3012	Black 3629 7901 ⁽¹⁾	S2 type Black IP55 1421 2111 ⁽¹⁾ Black IP65 1423 2111 Red IP65 1424 2111	200 mm 1400 1020 320 mm 1400 1032 ⁽¹⁾ 500 mm 1400 1050	1 st contact NO/NC 3999 0021 ⁽²⁾⁽³⁾ 2 contacts NO/NC 3999 0022 ⁽²⁾⁽³⁾ 1 contact NC 3999 0701 ⁽⁴⁾⁽⁵⁾ 1 contact NO 3999 0702 ⁽⁴⁾⁽⁵⁾				
	4 P	2915 4012	2921 4012								
ND 200 A	3 P	2915 3021	2921 3020								
	4 P	2915 4021	2921 4020								
ND 250 A	3 P	2915 3025	2921 3025								
	4 P	2915 4025	2921 4025								
ND 315 A	3 P	2915 3031	2921 3031								
	4 P	2915 4031	2921 4031								
ND 400 A	3 P	2915 3041	2921 3041								
	4 P	2915 4041	2921 4041								
ND 500 A	3 P	2915 3051	2921 3051								
	4 P	2915 4051	2921 4051								
630 A	3 P	2900 3063	2900 3063					Black 2799 7012 ⁽¹⁾ Red 2799 7013	S4 type Black IP65 1443 3111 ⁽¹⁾ Red / Yellow IP65 1444 3111	200 mm 1401 1520 320 mm 1401 1532 ⁽¹⁾ 400 mm 1401 1540	1 st contact NO/NC 2799 0001 2 nd contact NO/NC 2799 0002
	4 P	2900 4063	2900 4063								
800 A	3 P	2900 3080	2900 3080								
	4 P	2900 4080	2900 4080								
1250 A	3 P	2900 3120	2900 3120								
	4 P	2900 4120	2900 4120								
1600 A	3 P	2900 3160	2900 3160								
	4 P	2900 4160	2900 4160								

(1) Standard.

(2) Auxiliary signal contact - Type S.

(3) For direct operation.

(4) For external operation.

(5) Auxiliary signal contact - Type U.