

## References

### Front operation - Switch body with a shunt trip coil 230 VAC

Rating (A)	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	Auxiliary contact position	Auxiliary contact tripping	Terminal shrouds	Terminal screens	Inter phase barrier							
250 A	3 P	3500 3026	Black 3999 6203	S3 type Black IP55 1431 3511 <sup>(1)</sup>	200 mm 1401 1520 320 mm 1401 1532 <sup>(1)</sup>	1 <sup>st</sup> contact NO/NC 3999 0051 2 <sup>nd</sup> contact NO/NC 3999 0052	1 contact NO/NC 3999 0031	3 P 3998 3040 <sup>(2)</sup> 4 P 3998 4040 <sup>(2)</sup>									
	4 P	3500 4026															
400 A	3 P	3500 3041															
	4 P	3500 4041															
630 A	3 P	3500 3064															
	4 P	3500 4064															
800 A	3 P	3500 3081		S3 type Red/Yellow IP55 1432 3511					3 P 3998 3063 <sup>(2)</sup> 4 P 3998 4063 <sup>(2)</sup>								
	4 P	3500 4081															
1250 A	3 P	3500 3121								3 P 2998 3120 <sup>(2)</sup> 4 P 2998 4120 <sup>(2)</sup>	3 P 2998 0003 4 P 2998 0004						
	4 P	3500 4121															
1600 A	3 P	3500 3161															
	4 P	3500 4161															
1800 A	3 P	3500 3180															included
	4 P	3500 4180															

(1) Standard.

(2) Top/bottom.

### Side operation - Switch body with a shunt trip coil 230 VAC

Rating (A)	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	Auxiliary contact position	Auxiliary contact tripping	Terminal shrouds	Terminal screens	Inter phase barrier								
250 A	3 P	3505 3026	Black 3999 6012 <sup>(1)</sup> Red 3999 6013	S3 type Black IP55 1435 3511 <sup>(1)</sup>	200 mm 1403 1520	1 <sup>st</sup> contact NO/NC 3999 0051 2 <sup>nd</sup> contact NO/NC 3999 0052	1 contact NO/NC 3999 0031	3 P 3998 3040 <sup>(2)</sup> 4 P 3998 4040 <sup>(2)</sup>										
	4 P	3505 4026																
400 A	3 P	3505 3041																
	4 P	3505 4041																
630 A	3 P	3505 3064									S3 type Red IP55 1436 3511					3 P 3998 3063 <sup>(2)</sup> 4 P 3998 4063 <sup>(2)</sup>		
	4 P	3505 4064																
800 A	3 P	3505 3081								3 P 2998 3120 <sup>(2)</sup> 4 P 2998 4120 <sup>(2)</sup>	3 P 2998 0003 4 P 2998 0004							
	4 P	3505 4081																
1250 A	3 P	3505 3121																
	4 P	3505 4121																
1600 A	3 P	3505 3161																included
	4 P	3505 4161																
1800 A	3 P	3505 3180															included	
	4 P	3505 4180																

(1) Standard.

(2) Top/bottom.