

FUSERBLOC

Fuse combination switches

for industrial fuses up to 1250 A

References (continued)

NFC and DIN - Direct operation - 25 to 125 A

Rating (A) Fuse size Frame size	No. of poles	Direct side operation	Direct front operation	Direct handle	Auxiliary contacts	Terminal shrouds	Cage terminals	Lock for fuse protection cover	Handle key interlocking accessories ⁽⁶⁾						
25 A 10 x 38 0	3 P		3631 3002	Black 3629 4012 ⁽¹⁾⁽²⁾	A-type 1 contact NO/NC 3999 0001 ⁽³⁾ A-type 2 contacts NO/NC 3999 0002 ⁽³⁾	Standard	Standard	Standard							
	3 P + switched neutral		3631 4002												
	3 P + solid neutral		3631 5002												
CD 32 A 10 x 38 0	3 P		3631 3003												
	3 P + switched neutral		3631 4003												
	3 P + solid neutral		3631 5003												
32 A 14 x 51 0	3 P		3631 3004												
	3 P + switched neutral		3631 4004												
	3 P + solid neutral		3631 5004												
50 A 14 x 51 1	2 P	3615 2005	consult us							Black 3629 7900 ⁽⁵⁾⁽²⁾	A-type 1 contact NO/NC 3999 0021 ⁽³⁾ A-type 2 contacts NO/NC 3999 0022 ⁽³⁾	Standard	Standard	3999 8906	3629 7903
	3 P	3615 3005	consult us												
	4 P	3615 6005	consult us												
63 A 00C 2	2 P	3615 2006	consult us												
	3 P	3615 3006	consult us												
	4 P	3615 6006	consult us												
100 A 22 x 58 3	2 P	3615 2010	consult us	Black 3629 7901 ⁽⁵⁾⁽²⁾	A-type 1 contact NO/NC 3999 0021 ⁽³⁾ A-type 2 contacts NO/NC 3999 0022 ⁽³⁾	2 P 3998 2016 ⁽⁴⁾ 3 P 3998 3016 ⁽⁴⁾ 4 P 3998 4016 ⁽⁴⁾	3 P 5400 3016 4 P 5400 4016	3999 8912	3629 7913						
	3 P	3615 3010	consult us												
	4 P	3615 6010	consult us												
125 A 22 x 58 3	2 P	3615 2011	consult us												
	3 P	3615 3011	consult us												
	4 P	3615 6011	consult us												
125 A 00 3	2 P	3615 2012	consult us												
	3 P	3615 3012	consult us												
	4 P	3615 6012	consult us												

(1) Direct front operation.

(2) Standard.

(3) Maximum 2 contacts.

(4) Top or bottom.

(5) Direct right side operation.

(6) Locking using RONIS EL11AP lock (lock not included).