

References

BS88 - Front and side operation - Switch body with a shunt trip coil - 230 VAC

| Rating (A) Fuse ⁽¹⁾ | No. of poles | Front operation Switch body | Side operation Switch body | Direct handle ⁽²⁾ | External handle | Shaft for external handle | Auxiliary contact position | Auxiliary contact tripping | Terminal shrouds ⁽³⁾ | Terminal screens ⁽⁴⁾ | Inter phase barrier |
|-----------------------------------|--------------|--------------------------------|-------------------------------|--|---|--|--|--|---------------------------------|--|--|
| 250 A B1-B2-B3 | 3 P | 3660 3026 | 3665 3026 | Front operation Black 3999 6012 | | | | | 3 P 3998 3040 | | |
| | 4 P | 3660 6026 | 3665 6026 | | | | | | | | |
| 400 A B1-B2-B3-B4 | 3 P | 3660 3041 | 3665 3041 | Side operation Black 3999 6012 | S3 type | | | | 4 P 3998 4040 | | |
| | 4 P | 3660 6041 | 3665 6041 | | | | | | | | |
| 630 A C1-C2 | 3 P | 3660 3064 | 3665 3064 | Front operation Black IP55 1431 3511 ⁽²⁾ Red IP55 1432 3511 | | Front operation 200 mm 1401 1520 320 mm 1401 1532 ⁽²⁾ | 1 st contact NO/NC 3999 0051 | 1 contact NO/NC 3999 0031 | 3998 3063 | | |
| | 4 P | 3660 6064 | 3665 6064 | | | | | | | | |
| 800 A C1-C2-C3 | 3 P | 3660 3080 | 3665 3080 | Front operation Black 3999 6012 | Side operation Black IP55 1435 3511 ⁽²⁾ Red IP55 1436 3511 | Side operation 200 mm 1403 1520 | | | | | |
| | 4 P | 3660 6080 | 3665 6080 | | | | | | | | |
| 1250 A D1 | 3 P | 3660 3121 | 3665 3121 | Side operation Black 3999 6012 | | | | | | 3 P 3998 3120 4 P 3998 4120 | 3 P 2998 0003 4 P 2998 0004 |
| | 4 P | 3660 6121 | 3665 6121 | | | | | | | | |

(1) For the fuses: see page 230 "BS88 industrial fuselinks".

(2) Standard.

(3) Top/bottom.

(4) Bottom terminals protection screen as standard.