

NFC and DIN - External front and right side operation - 160 to 1250 A

Rating (A) / Fuse / Frame size	No. of poles	Switch I-0	Changeover switch I-0-II	External front handle	TEST external front handle	External right side handle	Changeover external front handle	Shaft for external handle	Auxiliary contacts	Terminal shrouds ⁽²⁾	Integrated solid neutral link	
160 A 00 13	2 P	3831 2015							U-type	2 P 3998 2016 3 P 3998 3016 4 P 3998 4016	3829 9320	
	3 P	3831 3015	3870 3015									
	4 P	3831 6015	3870 6015									
160 A 0 14	2 P	3831 2016		S2 type	S2 type	S2 type	S2 type	320 mm 1400 1032	1 contact 3999 0600⁽³⁾	2 P 3998 3016 3 P 3998 3016 4 P 3998 4016	3829 9320	
	3 P	3831 3016⁽¹⁾	3870 3016	Black IP55 1421 2111	Black IP65 1423 2115	Black IP55 1425 2111	Black IP55 1421 2113					
	4 P	3831 6016⁽¹⁾	3870 6016									
250 A 1 15	2 P	3831 2024		Red/Yellow IP65 1424 2111	Red/Yellow IP65 1424 2115	Red/Yellow IP65 1428 2111	Red/Yellow IP65 1424 2113		U-type	2 P 3998 2025 3 P 3998 3025 4 P 3998 4025	3829 9325	
	3 P	3831 3024⁽¹⁾	3870 3024									
	4 P	3831 6024⁽¹⁾	3870 6024									
400 A 2 16	2 P	3831 2039							1 contact 3999 0600⁽⁴⁾	2 P 3998 3025 3 P 3998 3025 4 P 3998 4025	3829 9339	
	3 P	3831 3039⁽¹⁾	3870 3039									
	4 P	3831 6039⁽¹⁾	3870 6039									
630 A 3 17	2 P	3811 2063		S3 type						2 P 3898 2080 3 P 3898 3080 4 P 3898 4080	3829 9308	
	3 P	3811 3063⁽¹⁾		Black IP65 1433 3111								
	4 P	3811 6063⁽¹⁾										
800 A 3 17	2 P	3811 2080		Red/Yellow IP65 1434 3111		S3 type		320 mm 1400 1232		2 P 3898 2120 3 P 3898 3120 4 P 3898 4120	3829 9312	
	3 P	3811 3080										Black IP65 1437 3111
	4 P	3811 6080										
800 A 4 18	2 P	3811 2081		S4 type			Red/Yellow IP65 1438 3111			2 P 3898 2120 3 P 3898 3120 4 P 3898 4120	3829 9312	
	3 P	3811 3081		Black IP65 1443 3111								
	4 P	3811 6081										
1250 A 4 18	2 P	3811 2120		Red/Yellow IP65 1444 3111						2 P 3898 2120 3 P 3898 3120 4 P 3898 4120	3829 9312	
	3 P	3811 3120										
	4 P	3811 6120										

(1) Available enclosed (see "Enclosed fuse switches" page XXX).

(2) Top/bottom.

(3) Maximum 4 contacts.

(4) Maximum 8 contacts.