

SIRCOVER

Manual changeover switches
from 125 to 3200 A

References (continued)

SIRCOVER Bypass

Rating (A)	No. of poles	Switch body I-0-II	Direct handle	External handle	Shaft for external handle	Bridging bar	Auxiliary contact	Terminal shrouds	Terminal screens							
125 A	3 + 6 P	4100 7013 ⁽¹⁾	Black 4199 5012	S2 type Black IP55 1421 2113 ⁽²⁾ Black IP65 1423 2113	200 mm 1400 1020 320 mm 1400 1032 ⁽²⁾	4109 0019	1 st /2 nd contact NO/NC 4109 0021 ⁽³⁾	3 P 2694 3014 ⁽⁴⁾⁽⁵⁾ 4 P 2694 4014 ⁽⁴⁾⁽⁵⁾	3 P 1509 3012 4 P 1509 4012							
	4 + 8 P	4100 9013 ⁽¹⁾														
160 A	3 + 6 P	4100 7016 ⁽¹⁾														
	4 + 8 P	4100 9016 ⁽¹⁾														
200 A	3 + 6 P	4100 7019														
	4 + 8 P	4100 9019														
250 A	3 + 6 P	4100 7025 ⁽¹⁾								Black 2799 7052	S3 type Black IP65 1433 3113	200 mm 1401 1520 320 mm 1401 1532 ⁽²⁾	4109 0025	1 st /2 nd contact NO/NC 4109 0021 ⁽³⁾	3 P 2694 3021 ⁽⁴⁾⁽⁵⁾ 4 P 2694 4021 ⁽⁴⁾⁽⁵⁾	3 P 1509 3025 4 P 1509 4025
	4 + 8 P	4100 9025 ⁽¹⁾														
400 A	3 + 6 P	4100 7039 ⁽¹⁾														
	4 + 8 P	4100 9039 ⁽¹⁾														
500 A	3 + 6 P	4100 7050 ⁽¹⁾														
	4 + 8 P	4100 9050 ⁽¹⁾														
630 A	3 + 6 P	4100 7063 ⁽¹⁾														
	4 + 8 P	4100 9063 ⁽¹⁾														
800 A	3 + 6 P	4100 7080 ⁽¹⁾	Black 2799 7012	Black IP65 4199 7146	200 mm 2799 3015 320 mm 2799 3018 ⁽²⁾ 450 mm 2799 3019	4109 0080	1 st /2 nd contact NO/NC 4109 0021 ⁽³⁾	3 P 2694 3051 ⁽⁴⁾⁽⁵⁾ 4 P 2694 4051 ⁽⁴⁾⁽⁵⁾	3 P 1509 3063 ⁽⁶⁾ 4 P 1509 4063 ⁽⁶⁾							
	4 + 8 P	4100 9080 ⁽¹⁾														
1250 A	3 + 6 P	4100 7120 ⁽¹⁾														
	4 + 8 P	4100 9120 ⁽¹⁾														
1600 A	3 + 6 P	4100 7160 ⁽¹⁾														
	4 + 8 P	4100 9160 ⁽¹⁾														

(1) Available enclosed (see "Enclosed changeover switches" page 625).

(2) Standard.

(3) 2 pieces supplied, one for position I and one for position II.

(4) To shroud front switch top and bottom 3 references required.

(5) To fully shroud front, rear, top and bottom 6 references required.

(6) 2 pieces supplied, one for top side and another for bottom side.