

## References

Rating (A)	No. of poles	Power supply	ATyS S	Bridging bars	Terminal shrouds	Voltage tap	Terminal retainer	DIN rail
40 A	4 P	24/48 VDC	9506 <b>4004</b>	4 P 9509 <b>4012</b>	Source side 2 pieces 9594 <b>4012</b>  Load side 2 pieces 9594 <b>9012</b>	9599 <b>4001</b>	2 pieces 9599 <b>4003</b>	4 modules 9599 <b>4002</b>
	4 P	12 VDC	9505 <b>4004</b>					
	4 P	2 x 230 VAC	9513 <b>4004</b>					
	4 P	230 VAC	9503 <b>4004</b>					
63 A	4 P	24/48 VDC	9506 <b>4006</b>					
	4 P	12 VDC	9505 <b>4006</b>					
	4 P	2 x 230 VAC	9513 <b>4006</b>					
	4 P	230 VAC	9503 <b>4006</b>					
80 A	4 P	24/48 VDC	9506 <b>4008</b>					
	4 P	12 VDC	9505 <b>4008</b>					
	4 P	2 x 230 VAC	9513 <b>4008</b>					
	4 P	230 VAC	9503 <b>4008</b>					
100 A	4 P	24/48 VDC	9506 <b>4010</b>					
	4 P	12 VDC	9505 <b>4010</b>					
	4 P	2 x 230 VAC	9513 <b>4010</b>					
	4 P	230 VAC	9503 <b>4010</b>					
125 A	4 P	24/48 VDC	9506 <b>4012</b>					
	4 P	12 VDC	9505 <b>4012</b>					
	4 P	2 x 230 VAC	9513 <b>4012</b>					
	4 P	230 VAC	9503 <b>4012</b>					