

Inline Straight Through Vacuum Filters


CT Series 3/4" - 6"

Features

- Compact design for space restrictions; min. service area
- Inlet above element for extended element life & maintenance intervals
- Corrosive resistant cast aluminum top with machined connections and integrated baffle design
- T-style design minimizes piping requirements
- Black powder coat carbon steel drop down bucket

Technical Specifications

- Vacuum Rating: medium vacuum service (33 to 1.3×10^{-3})
- Temp (continuous): min -15°F (-26°C) max 220°F (104°C)
- Filter change out differential: 15-20" H₂O over initial ΔP
- Polyester: 99%+ removal efficiency standard to 5 micron
- Paper: 99%+ removal efficiency standard to 2 micron



Inlet / Outlet		Assembly SCFM Rating	Assembly Part Number		Dimensions (inches)				Suggested Service Height (inches)	Approx. Weight (lbs)
Size	Type		Polyester	Paper	A	B	C	D		
3/4"	NPSC	25	CT-8451-075C	CT-8450-075C	8.45	1.00	5.00	5.96	5	3.5
1"	NPSC	40	CT-897-100C	CT-896-100C	13.24	1.52	7.00	10.16	9	12
1 1/4"	NPSC	60	CT-897-125C	CT-896-125C	13.24	1.52	7.00	10.16	9	12
1 1/2"	NPSC	80	CT-897-150C	CT-896-150C	13.24	1.52	7.00	10.16	9	11
2"	NPSC	175	CT-851-200C	CT-850-200C	12.77	1.98	9.00	8.97	9	16
2 1/2"	FNPT	210	CT-851-250C	CT-850-250C	12.77	1.98	9.36	8.97	9	15
3"	FNPT	300	CT-235P-300C	CT-234P-300C	18.60	2.70	13.50	12.92	10	30
4"	FNPT	520	CT-235P-400C	CT-234P-400C	18.60	2.70	13.50	12.92	10	26
6"	FNPT	1100	CT-275P-600C	CT-274P-600C	18.20	3.89	19.00	9.82	10	45

Note: CT 2" & 2 1/2" models: element seals on the base of the housing.

Learn More

For more information about Solberg products and finding the right solutions for your equipment needs, visit us at **SolbergMfg.com**.

Contact Us

solbergmfg.com/locations

