

Part No: 162B-020C

Valves

Y-Check Valve

Desc: 2 CPVC T/U Y-CHECK VALVE FPT EPDM

MSRP: 578.99

Part Code: 629

Weight(lbs): 5.055

Weight(kg): 2.293

Weight(gm): 2293

Size: 2


Color: GRAY

Material: CPVC

Connection Fipt (True Union)

Body Color Gray

O-Ring EPDM



A1 = 9-7/32

A = 7-5/8

B = 10-13/16

C = 12-13/16

D = 5-1/2

E = 3-23/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

