

Part No: 162B-030C

Valves

Y-Check Valve

Desc: 3 CPVC T/U Y-CHECK VALVE FPT EPDM

MSRP: 1147.16

Part Code: 629

Weight(lbs): 13.885

Weight(kg): 6.298

Weight(gm): 6298

Size: 3


Color: GRAY

Material: CPVC

Connection Fipt (True Union)

Body Color Gray

O-Ring EPDM



A1 = 13-7/16

A = 10-5/8

B = 15-11/32

C = 18-7/32

D = 7-9/16

E = 5-1/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

