

Part No: 163A-015CL

Valves

Y-Check Valve

Desc: 1-1/2 PVC CLR T/U Y-CHECK VLVE SOC FKM

MSRP: 362.56

Part Code: 628

Weight(lbs): 2.835

Weight(kg): 1.286

Weight(gm): 1286

Size: 1-1/2"


Color: CLEAR

Material: PVC

Connection Socket (True Union)

Body Color Clear

O-Ring FKM



A = 6- 5/8

A1 = 8- 1/8

B = 8- 1/4

C = 11

D = 4- 7/8

E = 3- 5/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

