

Part No: 163B-007CSR

Valves

Y-Check Valve

Desc: 3/4 CPVC T/U Y-CHECK VALVE SRFPT FKM

MSRP: 286.78

Part Code: 629

Weight(lbs): 1.003

Weight(kg): 0.455

Weight(gm): 455

Size: 3/4"


Color: GRAY

Material: CPVC

Connection SR Fipt (True Union)

Body Color Gray

O-Ring FKM



A = 4- 9/32

A1 = 5- 5/16

B = 6-13/32

C = 8

D = 3- 5/32

E = 2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

