

Part No: 163B-010C

Valves

Y-Check Valve

Desc: 1 CPVC T/U Y-CHECK VALVE FPT FKM

MSRP: 221.53

Part Code: 629

Weight(lbs): 1.51

Weight(kg): 0.685

Weight(gm): 685

Size: 1


Color: GRAY

Material: CPVC

Connection Fipt (True Union)

Body Color Gray

O-Ring FKM



C = 9

D = 3-5/8

E = 2-1/4

A1 = 6-1/16

A = 4-29/32

B = 7-5/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

