

Part No: 163B-010CLSR

Valves

Y-Check Valve

Desc: 1 PVC CLR T/U Y-CHECK VALVE SRFPT FKM

MSRP: 221.88

Part Code: 628

Weight(lbs): 1.387

Weight(kg): 0.629

Weight(gm): 629

Size: 1"


Color: CLEAR

Material: PVC

Connection SR Fipt (True Union)

Body Color Clear

O-Ring FKM



A = 4-29/32

A1 = 6- 1/16

B = 7- 5/16

C = 9

D = 3- 5/8

E = 2- 1/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

